

Tact the door contact, monitors any irregular opening or closing of doors and windows.

Fits anywhere and is easily mounted.

Compactly designed for easy mounting, Tact is barely noticeable and can be placed anywhere. When used with a base unit, Tact tracks whether someone opens a particular cupboard, window or door. With monitoring, this can be a cost-effective method of tracking medication schedules.

Possible Solutions:

- Place on cabinet doors to monitor open/close schedules
- Place on the bedroom door to monitor resident activity
- Place on the bathroom, entrance or backyard door

Uninterrupted monitoring.

Tact is equipped with a battery life of more than three years, and sends supervisory, tamper and low battery signals to the base unit. When an issue occurs, the monitoring station immediately receives a signal and acts accordingly.



Detailed Features

- Tamper protection to prevent unauthorized removal, sabotage or unsteady installation
- Randomized supervision signals for system integrity checks and troubleshooting
- LED serves as a fault and test mode indicator
- Easily mounts on door or window frames
- Compact and slim design
- Low battery detection
- Powerful magnet creates a 20mm space between Door Contact and the magnet

Technical Specifications

Compatible devices:	Nova; Apex; Apex V
Power:	Replaceable 1.5V AAA alkaline battery X 2
Battery life:	3.9 years*
Frequency:	433MHz
Ranges:	Up to 200 m [650 ft] in open space
Operating temperature:	-10°C to 50°C
Operating humidity:	Up to 95% non-condensing
Dimensions:	133 X 80 X 27.7 mm

*Battery life is calculated at an average of 20 activations a day